



PROFESSIONAL
by HARMAN

SRX Passive Bi-amp Tunings Table

Preset	Name	Channel 1	Channel 2	Channel 3 (HD)	Channel 4 (HD)
1	812 Main	812 Main	812 Main	812 Main	812 Main
2	812 Monitor	812 Monitor	812 Monitor	812 Monitor	812 Monitor
3	812 Speech	812 Speech	812 Speech	812 Speech	812 Speech
4	812 Sub 60	812 Sub 60	812 Sub 60	812 Sub 60	812 Sub 60
5	812 Sub 80	812 Sub 80	812 Sub 80	812 Sub 80	812 Sub 80
6	812 Sub 100	812 Sub 100	812 Sub 100	812 Sub 100	812 Sub 100
7	812 Sub 120	812 Sub 120	812 Sub 120	812 Sub 120	812 Sub 120
8	812 to 818 Sub 80Hz	818S SRX Top 80	812 Sub 80	818S SRX Top 80	812 Sub 80
9	812 to 818 Sub 60Hz	818S 60Hz	812 Sub 60	818S 60Hz	812 Sub 60
10	812 to 818 Sub 100Hz	818S 100Hz	812 Sub 100	818S 100Hz	812 Sub 100
11	812 to 818 Sub 120Hz	818S 120Hz	812 Sub 120	818S 120Hz	812 Sub 120
12	812 to 818 Sub Cardioid 80Hz	818S Cardioid 60	812 Sub 60	818S Cardioid 60	812 Sub 60
13	812 to 818 Sub Cardioid 60Hz	818S Cardioid 80	812 Sub 80	818S Cardioid 80	812 Sub 80
14	812 to 828 Sub 80Hz	828S SRX Top 80	812 Sub 80	828S SRX Top 80	812 Sub 80
15	812 to 828 Sub 60Hz	828S 60Hz	812 Sub 60	828S 60Hz	812 Sub 60
16	812 to 828 Sub 100Hz	828S 100Hz	812 Sub 100	828S 100Hz	812 Sub 100
17	812 to 828 Sub 120Hz	828S 120Hz	812 Sub 120	828S 120Hz	812 Sub 120
18	812 to 828 Sub Cardioid 80Hz	828S Cardioid 60	812 Sub 60	828S Cardioid 60	812 Sub 60
19	812 to 828 Sub Cardioid 60Hz	828S Cardioid 80	812 Sub 80	828S Cardioid 80	812 Sub 80
20	815 Main	815 Main	815 Main	815 Main	815 Main
21	815 Monitor	815 Monitor	815 Monitor	815 Monitor	815 Monitor
22	815 Speech	815 Speech	815 Speech	815 Speech	815 Speech
23	815 Sub 60	815 Sub 60	815 Sub 60	815 Sub 60	815 Sub 60
24	815 Sub 80	815 Sub 80	815 Sub 80	815 Sub 80	815 Sub 80
25	815 Sub 100	815 Sub 100	815 Sub 100	815 Sub 100	815 Sub 100
26	815 Sub 120	815 Sub 120	815 Sub 120	815 Sub 120	815 Sub 120
27	815 to 818 Sub 80Hz	818S SRX Top 80	815 Sub 80	818S SRX Top 80	815 Sub 80
28	815 to 818 Sub 60Hz	818S 60Hz	815 Sub 60	818S 60Hz	815 Sub 60
29	815 to 818 Sub 100Hz	818S 100Hz	815 Sub 100	818S 100Hz	815 Sub 100
30	815 to 818 Sub 120Hz	818S 120Hz	815 Sub 120	818S 120Hz	815 Sub 120
31	815 to 818 Sub Cardioid 80Hz	818S Cardioid 60	815 Sub 60	818S Cardioid 60	815 Sub 60
32	815 to 818 Sub Cardioid 60Hz	818S Cardioid 80	815 Sub 80	818S Cardioid 80	815 Sub 80
33	815 to 828 Sub 80Hz	828S SRX Top 80	815 Sub 80	828S SRX Top 80	815 Sub 80
34	815 to 828 Sub 60Hz	828S 60Hz	815 Sub 60	828S 60Hz	815 Sub 60
35	815 to 828 Sub 100Hz	828S 100Hz	815 Sub 100	828S 100Hz	815 Sub 100
36	815 to 828 Sub 120Hz	828S 120Hz	815 Sub 120	828S 120Hz	815 Sub 120
37	815 to 828 Sub Cardioid 80Hz	828S Cardioid 60	815 Sub 60	828S Cardioid 60	815 Sub 60
38	815 to 828 Sub Cardioid 60Hz	828S Cardioid 80	815 Sub 80	828S Cardioid 80	815 Sub 80

